

A class of its own.  
A sure bet!

The **GPCG 2 ISOLATOR** is a flexible solution for a wide range of fluid bed processes

- Drying
- Granulating
- Coating



Welcome to Glatt  
at the **ACHEMA!**  
Frankfurt am Main  
15 - 19 May 2006  
Hall 4.0  
Stand L16 - P22



Glatt technology  
Future today.

**Fluid bed systems**

Vertical granulators

Pan coaters

Product handling

Engineering

Services

Technical expertise from Glatt gives you the decisive edge in a hard competitive environment by providing utmost efficiency, reliability and productivity. We offer innovative solutions for every field of our expertise.



● **Glatt GmbH Process Technology**  
Werner-Glatt-Straße 1  
79589 Binzen / Germany  
Phone: +49 7621 6 64 0  
Fax: +49 7621 6 47 23  
eMail: info@glatt.com

● **Glatt Maschinen- & Apparatebau AG**  
Kraftwerkstrasse 6  
4133 Pratteln / Switzerland  
Phone: +41 61 8 26 47 47  
Fax: +41 61 8 26 48 48  
eMail: info@glatt.com

● **Glatt Ingenieurtechnik GmbH**  
Nordstraße 12  
99427 Weimar / Germany  
Phone: +49 3643 47 0  
Fax: +49 3643 47 12 31  
eMail: info@glatt-weimar.de

● **Glatt Air Techniques Inc.**  
20 Spear Road  
Ramsey, NJ 07446 / USA  
Phone: +1 201 8 25 87 00  
Fax: +1 201 8 25 03 89  
eMail: info@glattair.com

● **Glatt Norden ApS.**  
Skøjtevej 27 - 31  
2770 Kastrup / Denmark  
Phone: +45 48 14 22 44  
Fax: +45 48 14 22 55  
eMail: info@glattnorden.dk

● **Glatt Pharmatech SASU**  
Parc Technologique  
6, rue Louis Néel  
21000 Dijon / France  
Phone: +33 3 80 74 32 64  
Fax: +33 3 80 74 43 95  
eMail: info@glatt-pharmatech.fr

● **Glatt Protech Ltd.**  
Swannington Road  
Cottage Lane Ind. Est.  
Broughton Astley  
Leicester LE9 6TU / Great Britain  
Phone: +44 1455 28 58 58  
Fax: +44 1455 28 55 10  
eMail: info@glatt-protech.co.uk

[www.glatt.com](http://www.glatt.com)



Glatt fluid bed technology.

**GPCG 2 ISOLATOR**



©GLATT GMBH BINZEN - GPCG 2 ISOLATOR - 7221\_353 - MAY 2006 - EN - NEUBERGER.DESIGN

GRANULATING  
DRYING  
COATING



Total containment.  
Safety first!

Now you can test a wide variety of products and processes in the lab on just one single machine: the **GPCG 2 ISOLATOR**.

- Customised handling
- Clever cleaning system
- Intelligent isolator technology



**Customised handling**

Whether RTP port, washing chamber, tubing system with continuous liner or a combination of these systems – the design is as flexible as your requirements.

**Clever cleaning system**

Never get your hands dirty again! Integrated, automatic WIP system cleaning. Perfect accessibility for the manual cleaning of the isolator housing. And naturally with centralised waste water disposal.

**Intelligent isolator technology**

Push/push filters in the supply and exhaust air guarantee contamination-free filter replacement.

Everything under control!

**GPCG 2 LabSystem and GPCG 2 ISOLATOR.**  
An unbeatable combination.

- Maximum flexibility
- Integrated control
- Plug & Play



**Maximum flexibility**

For processes and products without total containment requirements: simply use it like a conventional GPCG 2 LabSystem. For drying, granulating and Wurster coating.

**Integrated control**

Maximum performance with optimal operability. Touch screen, developer or recipe mode, data acquisition and transmission. A central control for everything – independent of total containment mode or manual operation. Sometimes less is simply more.

**Plug & Play**

Plug it in and go! No complicated installation, no effort, no trouble. Just connect it and you're off. It's that simple!

**NEW!**